



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase.

Features & Benefits

Part of a Standard Loss System: When combined with Infinium Core Trunks and Infinium Core Cassettes	Multimode total channel connection loss: 2.5 dB, Multimode total channel connection return loss: 16 dB
Individual Patch Cable Assembly – Standard Insertion Loss: 0.50 dB Insertion loss	Compliance: BAA or TAA Compliant
Flexible Polarity: A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable	Bend-insensitive fiber for optimal cable management and ease of installation
TIA Channel Compliant	Dust caps pre-installed

Specifications

General Info

Product Line	Ortronics	Country Of Origin	Mexico
Type	Fiber Patch Cord		

Dimensions

Product Length US	9.0 m
-------------------	-------

Technical Information

Jacket Application	Plenum Rated	Simplex/Duplex	Duplex
Jacket Rating	FT6 Rated, OFNP Rated		