



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase.

## Features & Benefits

|  |  |
|--|--|
| Part of a Standard Loss System: When combined with Infinium Core Trunks and Infinium Core Cassettes        | Multimode total channel connection loss: 2.5 dB, Multimode total channel connection return loss: 16 dB |
| Individual Patch Cable Assembly – Standard Insertion Loss: 0.50 dB Insertion loss                          | Compliance: BAA or TAA Compliant   |
| Flexible Polarity: A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable | Bend-insensitive fiber for optimal cable management and ease of installation                           |
| TIA Channel Compliant  | Dust caps pre-installed  |

## Specifications

### General Info

|              |                  |                   |        |
|--------------|------------------|-------------------|--------|
| Product Line | Ortronics        | Country Of Origin | Mexico |
| Type         | Fiber Patch Cord |                   |        |

### Dimensions

|                   |        |
|-------------------|--------|
| Product Length US | 15.0 m |
|-------------------|--------|

### Technical Information

|                    |                       |                |        |
|--------------------|-----------------------|----------------|--------|
| Jacket Application | Plenum Rated          | Simplex/Duplex | Duplex |
| Jacket Rating      | FT6 Rated, OFNP Rated |                |        |