



Pass and Seymour  
Pin & Sleeve Watertight 60A 3ØY 120V/208V Connector  
Part No. PS560C9W



Four pole, Five wire, Pin and Sleeve Connector. 60 amp, 3Y, 120/208 volt.

## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Commercial
Standard	UL Listed		

### Dimensions

Product Width US	4.5 in	Product Height US	4.7 in
Product Length US	10.9 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	151347	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

---

Number of Wires	5	Amperage	60 A
Number of Poles	4-Way	Wire Size	2 AWG
Voltage	120.0 V		

---