




Pass and Seymour  
Decorator Openings, Six Gang, 302/304 Stainless Steel  
Part No. SS266



Smooth Metal Wall Plate 6-Gang Decorator 302/304 Stainless Steel

## Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032"  
nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel  
for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants,  
and other industrial, institutional, and commercial applications where  
corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as  
well as special Panel plates up to 5-gangs high  
and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom  
punched with over 300 opening styles.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA

### Dimensions

Product Width US	11.82 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

### Technical Information

Cutout	Decorator	Thickness	0.032 in
Number of Gangs	6		