



Pass and Seymour
Thermoplastic Two-Gang Decorator Wall Plate, Light Almond
Part No. TP262LACC30



The TradeMaster® thermoplastic 2-gang decorator wall plate provides maximum durability in plastic wall plates. Self-extinguishing nylon construction makes these wall plates virtually unbreakable. They are 3/16 of an inch higher and wider than typical plastic wall plates - not enough to be apparent to the eye, but the extra size cuts cost by reducing dry wall rework.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only)

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond

Preferred for hospital, industrial, institutional, and other high-abuse applications

Nominal thickness, .070 inch

Specifications

General Info

| | | | |
|--------------------|------------------------|-----------------|-----------------------|
| Product Line | Pass & Seymour | Color | Light Almond |
| Country Of Origin | United States | Wall Plate Type | Dimmer/Switch, Outlet |
| Application Sector | Residential/Commercial | Standard | CSA, UL514 |
| Type | Wall Plate | | |

Dimensions

| | | | |
|-------------------|-----------|------------------|---------|
| Product Width US | 4.75 in | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-----------------|-----------|---------------|----------------|
| Cutout | Decorator | Thickness | 0.07 in |
| Number of Gangs | 2 | Mounting Type | Exposed Screws |
