



Pass and Seymour  
20A 125V Fed Spec-Grade Tamper-Resistant USB Type A/A Outlet, White  
Part No. TR5362USBW



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

- Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices. One-piece heat-treated triple-wipe brass power contacts.
- AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects. Multiple color options available.
- Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. Stainless steel auto-ground clips assure positive ground.
- Wire Size: #14 - #10 AWG Copper Conductor Only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Vietnam
Number of Receptacles	2	Features	USB-A Charging
Outlet Type	Commercial, Indoor, Tamper-Resistant, USB-Charging	Application Sector	Commercial
Standard	CSA Listed, cULus, FSUL, UL Listed, RoHS	Warranty Type	1-Year Limited Warranty
Type	Outlet		

### Dimensions

---

Product Width US	1.693 in	Product Depth US	1.392 in
------------------	----------	------------------	----------

---

Product Height US	2.677 in
-------------------	----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

---

USB Amperage	3.1 A	Number of USBs	2
--------------	-------	----------------	---

---

USB Power Output	15 W	Temperature Rating	-40° - 60° C
------------------	------	--------------------	--------------

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

---

Voltage	125 V
---------	-------

---