

DATA SHEET



4-Port USB Wall Charger - AC to USB Adapter, 5V 4.8A Output

Simultaneously charge four mobile devices from a single outlet

OVERVIEW

The 4-Port USB Wall Charger - AC to USB Adapter is an ideal solution for charging a mobile device at home, in the office, or on the road. This adapter provides a power output of 5 volts and 4.8 amps for device charging. Three ports provide 5 volts and 1 amp and the fourth port provides 5 volts and 2.4 amps, with a max output of 4.8 amps of power for device charging from this adapter when it plugged into an AC outlet.

FEATURES

- 5V, 4.8A total maximum output
- 4 standard USB-A ports
- Compact size
- Foldable AC prongs

ITEM DESCRIPTION

20277 4-Port USB Wall Charger - AC to USB Adapter, 5V 4.8A Output

DATA SHEET

SPECIFICATIONS: 4-Port USB Wall Charger - AC to USB Adapter, 5V 4.8A Output

ELECTRICAL OUTPUT CHARACTERISTICS:

Port 1

- Output voltage: $5 \pm 0.25V$
- Regulation: $\pm 5\%$
- Rated current: 2.4A

Port 2

- Output voltage: $5 \pm 0.25V$
- Regulation: $\pm 5\%$
- Rated current: 1A

Port 3

- Output voltage: $5 \pm 0.25V$
- Regulation: $\pm 5\%$
- Rated current: 1A

Port 4

- Output voltage: $5 \pm 0.25V$
- Regulation: $\pm 5\%$
- Rated current: 1A

ELECTRICAL INPUT CHARACTERISTICS:

- Input voltage range: 90-264V AC
- Nominal input voltage: 100-240V AC
- Frequency range: 47-63Hz
- Input current with full load: $\leq 0.5A$
- Inrush current: 20A
- Efficiency: $\geq 80\%$
- Standby power loss: $\leq 0.3W$

OPERATING ENVIRONMENT:

Temperature

- Operating: -5° - $+35^{\circ}C$
- Storage: -10° - $+50^{\circ}C$

Humidity

- Operating: 10% - 90% relative humidity (non-condensing)
- Storage: 5% - 95% relative humidity (non-condensing)

PHYSICAL CHARACTERISTICS:

- Dimensions (HxWxD): 3.00 x 1.15 x 2.25in



Legrand, North and Central America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Follow Us

