

Simplese (NV-A4D).

Specifications

Zones 1-4 Power Amplifier Outputs

Continuous Average Output Power	30W (15W x 2)
Two channels driven 30-20kHz @ 1% THD	
Rated Distortion (1/2 Power)	0.40%
Rated Impedance	6 ohm
Damping Fator	50+
Frequency Response	20-20kHz

Preamplifier Section

Variable Output	0-600mV RMS
Fixed Output	600mV RMS
Impedance	600 ohm

Source Inputs 1-4

Input Impedance	10K
Input Sensitivity for Rated Power	300mV RMS
Input Overload	3V RMS

Emitter Outputs

Source Outputs	4
Output Drive Current	100mA
Output Drive Voltage	5VDC
Source 1 and 2	38kHz/56kHz Selectable
Source 3 and 4	38kHz Fixed

System

System On	5VDC @50mA
External Mute	3-12VDC

Power Requirements

Power Supply	90-260VAC 50/60Hz
Power Consumption all channels driven to full-rated power	140W
Power Consumption average operating conditions	30W
Power Consumption no signal	Less than 10W

Regulatory Approvals

CE
C-Tick
ETL

Physical Specifications

Unit Size (mm)	44 H x 430 W x 250 D
Unit Size (inch)	1 3/4 H x 17 W x 10 5/8 D
Shipping Size (mm)	254 H x 508 W x 355.6 D
Shipping Size (inch)	10 H x 20 W x 14 D
Unit Weight (kg)	2.95
Unit Weight (lbs)	6.5
Shipping Weight (kg)	6.80
Shipping Weight (lbs)	15

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904

Office Direct: 859.817.7200

Email: sales@nuvotechnologies.com

Web: www.nuvotechnologies.com