

Pass & Seymour


Decorator Receptacles PlugTail[™] Devices Spec Grade 15 & 20A, 125V


PT26252, PT26352

PlugTail[™]. The fastest, most consistent and reliable wiring devices — ever.

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

The toughest and safest decorator receptacle available.







Decorator Receptacles PlugTail[™] Devices Spec Grade 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rati A.	ng V.	Color	NEMA Config. No.		
Duplex Receptad	Duplex Receptacles					
PT26252-I	15	125	lvory	5-15R		
PT26252-W	15	125	White	5-15R		
PT26252	15	125	Brown	5-15R		
PT26252-GRY	15	125	Gray	5-15R		
PT26252-BK	15	125	Black	5-15R		
PT26252-RED	15	125	Red	5-15R		
PT26252-LA	15	125	Light Almond	5-15R		
PT26352-I	20	125	lvory	5-20R		
PT26352-W	20	125	White	5-20R		
PT26352	20	125	Brown	5-20R		
PT26352-GRY	20	125	Gray	5-20R		
PT26352-BK	20	125	Black	5-20R		
PT26352-RED	20	125	Red	5-20R		
PT26352-LA	20	125	Light Almond	5-20R		

Catalog Number	Wire Type	Wire Length		
PlugTail Connectors — Right Angle				
PTRA6STR PTRA6SOL	Stranded Solid	6" 6"		



For more information on these and other P&S products refer to our Product Guide or visit our web site.

Decorator Receptacles PlugTail[™] Devices Spec Grade 15 & 20A, 125V



3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498. Federal Specification WC596.


Performance	
Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" or 25" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

Plug Tail Receptacle Materials				
Face Back Body Line Contact Mounting St		Integral Ground System Assembly Drive Screw Auto-Ground Clip Steel	.036 260 Brass Zinc-Plated Steel Steel Tri-Drive Steel	

Plug Tail Connector Materials					
Housing	Polycarbonate	Contacts	.030 Brass		

Warranty

1 Year




Dimensions for 15 & 20 Amp








COMPLEMENTARY DEVICES & ACCESSORIES



PLUGTAIL[™] DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use

SWITCHES

Toggle

Toggle

Toggle

- Construction Grade
- Construction Grade Leaded
- Commercial Grade

■ Heavy-Duty Toggle


Heavy-Duty Lighted

Heavy-Duty Security

Heavy-Duty Locking

Construction Grade

Commercial Grade



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights

GFCIs

Specification Grade



WALL PLATES

- TradeMaster[®] Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok[®]
 Locking Devices
- Weatherproof Boxes & Covers

ALSO AVAILABLE...

- IEC 309 Industrial Products
- Flexcor[®] Wire Mesh Grips
- Bulk Solutions



P.O. Box 4822 Syracuse, NY 13221-4822 Phone: 1.800.776.4035 www.legrand.us/passandseymour

570 Applewood Crescent Vaughan, Ontario L4K 4B4 Phone:905.738.9195