



RHCL453PW

Energy-saving dimming for CFL, LED and Incandescent loads.


RHCL453P

radiant® dimmers help save energy simply, and as part of the radiant collection, now offer a better fit, form and finish. Compatible with CFL/LED dimmable bulbs (with the exception of 0-10V LED drivers), these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.

Features & Benefits

Adjustment dial allows users to adjust the bottom of the dimming range for a wide range of CFL and LED bulbs.

Convenient operation: combines ON/OFF paddle switch with separate slider for dimming control.



White LED glows when device is OFF to make dimmer easy to find in the dark.


Sleek, ergonomic design that matches today's styles.

Wider slide controller: for easier dimming operation.

RHCL453PW

- **Preset, Single Pole and 3-Way operation.**
- Constant memory returns lights to previous level after a power failure.
- Compatible with CFL/LED dimmable bulbs (with the exception of 0-10V LED drivers).
- No de-rating required in multi-gang applications.
- **Interchangeable face plates** available in eight colors (RHKIT*; sold separately).


3rd Party Compliance



Technical Information

Performance

Electrical	
Supply Voltage	120VAC
Ratings	450W CFL/LED; 700W Incandescent/Halogen
Frequency	60Hz
Installation	Single Pole or 3-Way
Environmental	
Application	Indoor Use Only
Mechanical	
Enclosure Material	Polycarbonate



RHCL453PW

Warranty

Lifetime

Ordering Information

radiant® CFL/LED Incandescent/Halogen Dimmers


Catalog Number	Description	Color	Voltage	Rating
RHCL453PTC	Preset, Single Pole and 3-Way	Three interchangeable Face Colors: Ivory, White, Light Almond	120VAC 60Hz	700W Inc/Halogen 450W CFL/LED
RHCL453PW	Preset, Single Pole and 3-Way	Face Color: White	120VAC 60Hz	700W Inc/Halogen 450W CFL/LED
RHCL453PGCCV4	Preset, Single Pole and 3-Way	Face Color: Graphite	120VAC 60Hz	700W Inc/Halogen 450W CFL/LED
RHCL453PDBCCV4	Preset, Single Pole and 3-Way	Face Color: Dark Bronze	120VAC 60Hz	700W Inc/Halogen 450W CFL/LED
RHCL453PNICCV4	Preset, Single Pole and 3-Way	Face Color: Nickel	120VAC 60Hz	700W Inc/Halogen 450W CFL/LED
RHKIT	Interchangeable Faces	Brown		
RHKITBK		Black		
RHKITGRY		Gray		
RHKITI		Ivory		
RHKITLA		Light Almond		
RHKITNI		Nickel		
RHKITW		White		
RHKITDB		Dark Bronze		

Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

Also available in the radiant® collection

- GFCI Receptacles
- Tamper-Resistant and Standard Duplex Receptacles
- Paddle Switches
- Fan Controls
- Sensors
- Timers
- Home Automation Controls
- USB Charging Devices
- Night Lights
- Screwless Wall Plates

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

