



## LYRIQ LOCAL SOURCE INPUT IN STUDIO DESIGN, GLOSS BLACK

AU5008-GB | [On-Q](#)

### FEATURES & BENEFITS

The lyriQ Local Source Input enables users to plug in devices like personal audio players locally for in-room entertainment. It automatically overrides the remote source music in the room and returns to the main source when the local source is turned off. It also includes a convenient RJ45 connection and adjustable gain control. Up to two local source inputs can be installed per zone, and it can be selected from the keypad or the On-Q remote.

- Automatically overrides the remote source
- For use with the lyriQ Audio System

### SPECIFICATIONS

#### GENERAL INFO

Color: Gloss Black  
Product Series: Studio

#### CONSTRUCTION INFORMATION

Spec 1: Voltage Requirements  
Installation Location: In-Wall

#### DIMENSIONS

Overall Dimensions (US): 4.91" H x 1.65" W x 2.125" D

#### CORD INFORMATION

Pinning:

1. Green/White Left Audio Ground (PreGND)
2. Green Left Audio
3. Orange/White Right Audio Ground (PreGND)
4. Blue IR (IR TX)
5. Blue/White Status (IR RX)
6. Orange Right Audio

7. Brown/White Ground
8. Brown Power (+24Vdc)

#### TECHNICAL INFORMATION

Frequency Response: 20 - 100 Hz  $\pm$  4 dB 100 - 20,000 Hz  $\pm$  2 dB

Humidity: Up to 90% RH (non-condensing)

IR Receive Frequency: 10 KHz  $\pm$  5 KHz to 110 KHz  $\pm$  5 KHz

Operating Temperature (Celsius): 0 to 55°C

Output And Line Out Connection: Audio Out: RJ45 Connection

Power Requirements: +24Vdc supplied by the Distribution Module

Storage Temperature: -25 to +75 Degrees Celsius