



INTERCOM DOOR UNIT, WEATHER RESISTANT, OIL RUBBED BRONZE

F7596-OB | [On-Q](#)

FEATURES & BENEFITS

This Intercom Door Unit is sure to increase the curb appeal of any home. It home runs from the enclosure for efficient installation and features a backlit button for easy operation at night. The door unit is the perfect addition to any intercom system.

- **Back lit button allows for easy operation at night.**
- **Easy installation with 110 punchdown connection.**
- **Available in five colors:** White, Antique Brass, Brushed Stainless, Oil-Rubbed Bronze and Shiny Brass.

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 5
Color: Oil Rubbed Bronze
Connection Type: 110 IDC Punchdown
Product Series: inQUIRE 1000
Type: Door Unit

ASSEMBLY/INSTALLATION INFORMATION

Mounting Hardware Included: Yes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

FCC Standard: Yes
UN SPSC: 43221525

CONSTRUCTION INFORMATION

Installation Location: Outdoor

DIMENSIONS

Depth (Metric): 3.8 cm
Depth (US): 1.5"
Height (Metric): 12.1 cm
Height (US): 4.75"

Width (Metric): 12.1 cm

Width (US): 4.75 in

CORD INFORMATION

Cord Length US: 325 Foot home-run

Pinning:

1. Blue/White Audio In (Speaker)
2. Blue Ground
3. Orange/White Power
4. Orange Audio Out (Microphone)
5. Green/White Relay (changing from Mic to Speaker)
6. Green Not Used
7. Brown/White Not Used
8. Brown Door Chime Activation (when doorbell button is pressed)

TECHNICAL INFORMATION

Frequency Response: up to 16kHz

Humidity: 90% Relative Humidity (Non-Condensing)

Mounting: Wall

Operating Temperature (Celsius): -25°C to 55°C

Power Peak: 2 W

Power RMS: 3 W

Product Fits Into: Double Gang Electrical Box

Speaker Depth (Metric): 28 mm

SpeakerDepth (US): 1.1 in

Speaker Impedance Load: 8 ohms

Supported Standards: FCC PART 15 B