

---

## ISOLATED GROUND RECEPTACLES

PSIG5266X | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### Straight Blade Plug 2pole 3wire 15amp 125volt Isolated Ground

Unit arrives completely ready-to-wire, cuts installation time significantly. Nylon housing provides impact and chemical resistance. Rugged two-piece cord grip provides more uniform cord retention. Internal dust shield keeps terminals free of contaminants. Tri-drive assembly screws are standard on all Specification Grade plugs and connectors. All 3-wire terminals located on the same plane, allows for quick wire termination from any angle. Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity. Cord-grip screws recessed to protect installer against screwdriver head slippage.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Isolated ground

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: Yes  
UL Listing No: No  
UN SPSC: 39121402  
UR: No

#### DIMENSIONS

Depth (US): 1.752"  
Height (US): 1.516"  
Width (US): 1.516"

#### TECHNICAL INFORMATION

Volts (AC): 125  
Grade Type: Specification

#### COUNTRY OF ORIGIN

Country Of Origin: MEXICO