



SPEC-GRADE WEATHER-RESISTANT 15A SELF-TEST DUPLEX GFCI, BROWN

1597TRWR | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

The self-test GFCI conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock™ Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

Make sure you can spot ground fault trips quickly and resolve them easily with GFCI Receptacles installed in the living space.

radiant® Screwless Wall Plate not included.

For detailed GFCI receptacle information, visit our GFCI Headquarters.

Meet code and reduce callbacks by pairing GFCI receptacles with AFCI breakers on kitchen and laundry room circuits. Learn more at www.legrand.us/gfci.



PRODUCT
ENVIRONMENTAL PROFILE

- Part of the radiant® collection
- Meets UL498 rating for Weather-Resistance
- New external back wire pressure plates.
- New posted terminal screws for faster installation.
- Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced.
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects meeting National Electrical Code® Tamper-Resistant requirements.
- Redesigned side wire cavity improves speed of side wire installation.
- Feed-thru wiring configuration allows GFCI to protect downstream receptacles.

- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
-

SPECIFICATIONS

GENERAL INFO

Color: Brown

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

cULus: Yes

Federal Spec: Yes

UL Standard: UL498 Attachment Plugs and Receptacles

CONSTRUCTION INFORMATION

Component 4: 78500703647

DIMENSIONS

Depth (US): 1.13"

Height (US): 4.19"

Width (US): 1.62"

Weight: 3.59 oz.

TECHNICAL INFORMATION

Amps: 15A

Material: Nylon

NEMA Configuration Number: 5-15R

Volts: 125

Volts (AC): 125 VAC

Capacity: 15A

Grade Type: Spec Grade

COUNTRY OF ORIGIN

Country Of Origin: CHINA