



## 6.0A ULTRA-FAST TYPE C/C USB CHARGERS WITH DUPLEX 15A TAMPER-RESISTANT OUTLET, WHITE

R26USBC6W | [radiant](#)

### FEATURES & BENEFITS

Install the fastest USB charger on the market. Charge your smartphones, tablets, and laptops up to 40% faster than 3-5A USB chargers, while enjoying the added power convenience of Tamper-Resistant outlets that meet NEC® requirements. Industry-leading charging capacity of 6.0A, shared between both ports. Protects children: patented shutter system helps prevent improper insertion of foreign objects - now with black "invisi-shutters" for an invisible effect. The external brass backwire pressure-plate and posted side-wire terminal screws make installation fast and easy.

RoHS compliant

radiant® Screwless Wall Plate not included.



- Ultra-fast USB charger with industry-leading 6A available thru USB ports
- Smart Chip technology to maximize charge speeds at each USB port.
- Reversible Type-C USB connector to accommodate latest mobile devices.
- Power outlets meet NEC® Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects—now with black "invisi-shutters" for an invisible effect preferred by end users.
- Back and side wire terminals accommodate #10-#14 AWG stranded and solid copper wire for installation flexibility; tightening torque: 12-14 lb.-in.
- The external brass backwire pressure-plate and posted side-wire terminal screws make installation fast and easy.
- Scalloped cover design and posted side-wire terminal screws allow for faster and easier installs.
- Score lines on device ears for easy removal prior to drywall routing.
- RoHS compliant.

### SPECIFICATIONS

### GENERAL INFO

Color: White

Available Colors: White, Light Almond, Ivory, Black, Nickel, Dark Bronze

Special Features: USB Configuration: (2) Type-C

USB Rating: Total 6.0A/ 3A per port

Style: USB Outlet

#### **LISTING AGENCIES/THIRD PARTY CERTIFICATIONS**

RoHS: Yes

CSA Listing Info: CSA C22.2 No. 223, CSA C22.2 No. 42

CSA Listed: Yes

cULus: Yes

UL Listing No: E140596

UL Standard: UL498, UL1321

#### **DIMENSIONS**

Depth (US): 1.67"

Height (US): 2.69"

Width (US): 1.74"

#### **TECHNICAL INFORMATION**

NEMA Configuration Number: 5-15R

Volts: 125

#### **COUNTRY OF ORIGIN**

Country Of Origin: CHINA