



ONE-GANG SCREWLESS WALL PLATE, WHITE

RWP26W | [radiant](#)

FEATURES & BENEFITS

A step above the standard with no unsightly screws, this modern, low-profile wall plate instantly elevates the look of radiant dimmers, switches, outlets, home automation controls and more.

Available in White, Ivory, Light Almond, Black, Brown and Gray, as well as three metallic finishes: Nickel, Dark Bronze and Antique Brass (all sold separately) to coordinate with most any decor.



- radiant screwless wall plates feature a modern low profile in keeping with today's design trends.
- Molded of rugged .065" thick polycarbonate for greater durability.
- One-piece subplate mounts over the device, allowing you to simply snap on the wall plate with ease.
- Subplate screws align devices to ensure proper positioning of the wall plate.
- An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.
- Opening accommodates all NEMA 26-opening devices.

SPECIFICATIONS

GENERAL INFO

Color: White

Special Features: Screwless

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 4: 78500732080

DIMENSIONS

Height (US): 4.94"
Width (US): 3.15"

TECHNICAL INFORMATION

Material: Polycarbonate

COUNTRY OF ORIGIN

Country Of Origin: UNITED STATES OF AMERICA