



Huawei 02311MNN Compatible 100GBase-CWDM4 QSFP28 Transceiver (SMF, 1271nm-1331nm, 2km, LC Duplex, DDM, C-Temp)



Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our [Warranty page](#).
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info			
Product Line	Ortronics	UPC Number	662875063353
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		
Dimensions			
Product Width US	18.35 mm	Product Depth US	122.0 mm
Product Height US	8.5 mm		
Technical Information			
Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	0 °C
Operating Temperature Max	70 °C	Connector Type	LC Duplex
Form Factor	QSFP28		