



Adva 1061701888-01 Compatible 10GBase-BX SFP+ Transceiver (SMF, Tx: 1330nm Rx: 1270nm, 10-20km, LC Duplex, DDM, I-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875066286
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	13.7 mm	Product Depth US	56.6 mm
Product Height US	12.8 mm		

Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 °C
Operating Temperature Max	85 °C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Wavelength	1330 nm
Form Factor	SFP+		