



Pressure Sensitive Door and Canopy Switch 15A 120VAC, 15A 250VAC

Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Requirements. Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007120011
Country Of Origin	Mexico	Switch Type	Canopy
Application Sector	Commercial, Residential	Standard	UL Listed
Type	Switch		

Dimensions

Product Width US	1.516 in	Product Depth US	1.344 in
Product Height US	4.031 in		

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Contact Rating	120/250 VAC, 15 Amp	Amperage	15 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2