



Canopy Switch, Interiors Only, with Leads, Plunger & Face Plate 15 Amp 120Vac, 15 Amp 250 Vac

Features & Benefits

Equipped with wire leads. 1200 and 1201 complete with metal box and plate. Only 14 oz. pressure actuates switch. Back box cold rolled steel. Plate is steel with a bronze coating.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL Listed

Technical Information

Contact Configuration	N-0	Operating Cycles	30000
Contact Rating	120/250 VAC, 15 Amp	Amperage	15 A
Action	SP	Number of Poles	Single Pole
Voltage	120.0 V	Environmental Conditions	Flammability: UL94 V2