

Double-Pole, Double-Throw Switch, 15A, 120/277V.



## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see <https://www.legrand.us/patents>.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit [www.legrand.us/electrical-wiring-devices/wall-plates](http://www.legrand.us/electrical-wiring-devices/wall-plates).

## Specifications

### General Info

|                   |                |          |           |
|-------------------|----------------|----------|-----------|
| Product Line      | Pass & Seymour | Color    | Brown     |
| Country Of Origin | Mexico         | Standard | UL Listed |

### Listing Agencies / 3rd Party Agencies

|                 |       |              |     |
|-----------------|-------|--------------|-----|
| CSA Listed      | Yes   | cULus Listed | Yes |
| CSA File Number | 17949 |              |     |

### Technical Information

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
| Wattage  | 2 W  | Voltage         | 120/277 V   |

---