



Pass and Seymour
Locking 20A Double Pole, Double Throw Switch
Part No. 1226L

Manual Controller Double-Pole, Double-Throw Switch, 20A,
120/277V, Locking.



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see <https://www.legrand.us/patents>.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates.

Specifications

General Info

| | | | |
|-------------------|----------------|----------|-----------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Standard | UL Listed |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------|-------|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 17949 | | |

Technical Information

| | | | |
|----------|---------|---------|-----|
| Amperage | 20 A | Wattage | 2 W |
| Voltage | 120.0 V | | |