



Pass and Seymour  
Locking Manual Controller  
Part No. 1250L



Locking Manual Controller, Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating, Tested to 3A, 24VDC rating.

## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Fiber terminal insulation barriers standard.

Bodies, covers, and toggles molded of durable nylon.

Locking Switches supplied with one 1498-NT key.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Single Pole-Double Throw and Double Pole-Double Throw.

Normally open.

## Specifications

### General Info

|                   |                |          |           |
|-------------------|----------------|----------|-----------|
| Product Line      | Pass & Seymour | Color    | Gray      |
| Country Of Origin | Mexico         | Standard | UL Listed |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.5 in   | Product Depth US | 1.469 in |
| Product Height US | 3.281 in |                  |          |

### Listing Agencies / 3rd Party Agencies

|            |     |              |     |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

|                 |       |
|-----------------|-------|
| CSA File Number | 17949 |
|-----------------|-------|

Technical Information

|          |      |         |     |
|----------|------|---------|-----|
| Amperage | 15 A | Wattage | 1 W |
|----------|------|---------|-----|

|         |         |
|---------|---------|
| Voltage | 120.0 V |
|---------|---------|