

Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V.



## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|              |                |                   |        |
|--------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Standard     | UL Listed      |                   |        |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.5 in   | Product Depth US | 1.469 in |
| Product Height US | 3.281 in |                  |          |

### Listing Agencies / 3rd Party Agencies

|                       |         |              |     |
|-----------------------|---------|--------------|-----|
| CSA Listed            | Yes     | cULus Listed | Yes |
| CSA File Number       | 17949   |              |     |
| Technical Information |         |              |     |
| Amperage              | 20 A    | Wattage      | 1 W |
| Voltage               | 120.0 V |              |     |