

Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V.



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	Mexico	Standard	RoHS, UL Listed, CSA Listed

Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

cULus Listed

Yes

Technical Information

Operating Cycles

50000

Actuator

Toggle

Connection

Side Wire

Amperage

20 A

Voltage

120.0 V

Environmental Conditions

UL94 V2
