



Pass and Seymour
Tamper-Resistant Floor Box Assembly, One-Gang for Wood Sub-Floors, Brass Plate
Part No. 1542TRDR



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly
- Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring
- .032 inch thick brass triple-wipe power contacts for lasting retention
- Auto-ground clip assures positive ground

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	Country Of Origin	United States
Receptacle Type	5-15R	Number of Receptacles	1
Features	Recessed	Outlet Type	Commercial
Package Quantity	1	Application Sector	Commercial
Standard	cULus	Type	Outlet

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
---------------------	-----	----------	------

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

Voltage	125.0 V	Connection Type	Wired
---------	---------	-----------------	-------

Environmental Conditions	85% (relative humidity, non-condensing)
--------------------------	---
