



Tamper-Resistant Display Receptacle, 15A 125V With Brass Plate and plug.

Features & Benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly
- Easily accessed break-off line contact connecting tab for fast and easy split circuit wiring
- .032 inch thick brass triple-wipe power contacts for lasting retention
- Auto-ground clip assures positive ground

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	UPC Number	785007108767
Country Of Origin	United States	Material	Brass
Cover Type	Tamper-Resistant	Features	Recessed
Application Sector	Commercial	Wall Plate Included	No
Standard	cULus, FEDSPEC	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	2.75 in	Product Weight US	0.53 lb
------------------	---------	-------------------	---------

Product Depth US	1.825 in	Product Height US	4.5 in
------------------	----------	-------------------	--------

Product Length US	4.5 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Connection Location	Side Only	Number of Wires	3
---------------------	-----------	-----------------	---

Number of Gangs	1	Number of Poles	3-Way
-----------------	---	-----------------	-------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
----------------	--------	-------------------------	-------

Mounting Type	Screw Mount	Box Cover Position	Vertical
---------------	-------------	--------------------	----------

Wire Connection Type	Screw Terminals	Voltage	125.0 V
----------------------	-----------------	---------	---------

Environmental Conditions	85% (relative humidity, non-condensing)
--------------------------	---
