



Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected. Visual LED power identification of receptacles to ensure proper functionality for necessary loads. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Protects against shock caused by ground-fault occurrences. GFCI receptacles make it easier to fix trips with a reset button right on the device.

Hospital Grade GFCIs are subjected to additional performance requirements, including reliability, integrity, strength, and durability tests.

Conducts an industry-leading automatic self-test every 3 seconds. The trip indicator light flashes if the device fails the self-test, signaling the GFCI is to be replaced.

GFCIs prevent line-load reversal due to inadvertent miswire; there is no power to the face or downstream receptacles if wired incorrectly.

Auto-ground clip assures a positive ground to metal box.

Power-indicating amber LED provides visual indication of power being present at the receptacle.

Enhanced tamper-resistant automatic shutter system allows for easier plug insertion while inhibiting young children or others from inserting objects.

Equipped with patented SafeLock® protection. If critical components are damaged and ground-fault protection is lost, power to the receptacle is disconnected.

High-impact-resistant, thermoplastic construction for superior strength and durability.

FSUL listed (Federal Specification WC596).

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007289916
Country Of Origin	China	Number of Receptacles	2
Features	Indicator Lights	Outlet Type	GFCI, Self-Test, Tamper-Resistant
Application Sector	Residential	Warranty Type	1-Year Limited Warranty
Type	Duplex, GFCI, Tamper-Resistant		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Gangs	1
Amperage	15 A	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Mounting Type	Box