



Pass and Seymour  
**Discontinued - GFCI PI HG TR RECEP 15A, RED GN LED**  
Part No. 1597HGTRPIRED



Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected. Visual LED power identification of receptacles to ensure proper functionality for necessary loads. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

|   |  |
|---|--|
| Power Indicating Green LED flashes if the device needs to be replaced   | Hospital Grade GFCI specially designed and tested for rigorous healthcare applications                     |
| Tamper-Resistant automatic shutter system prevents insertion. Black shutters essentially ""disappear"" into the background for an invisible effect preferred by end users | The indicator light flashes if the device fails the self-test, signalling that the GFCI should be replaced |
| Two back-wire holes per termination add wiring flexibility, eliminate pigtailng and save box space  | High-impact-resistant, thermoplastic construction for superior strength and durability                     |
| Ground terminal back-wire for fast installation   | Auto-ground clip assures a positive ground to metal box  |
| FSUL Listed (Federal Specification WC596)   |  |

Specifications

General Info

|                   |                         |                       |  |
|-------------------|-------------------------|-----------------------|--|
| Product Line      | Pass & Seymour          | Color                 | Red  |
| Finish            | Matte                   | UPC Number            | 785007289787   |
| Country Of Origin | China                   | Number of Receptacles | 2  |
| Features          | Indicator Lights        | Outlet Type           | GFCI, Indoor, Residential, Self-Test, Tamper-Resistant |
| Warranty Type     | 1-Year Limited Warranty | Type                  | Duplex, GFCI, Tamper-Resistant, USB                    |

Additional Information

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

Technical Information

|                     |         |                      |     |
|---------------------|---------|----------------------|-----|
| Is Tamper-Resistant | Yes     | Number of Gangs      | 1   |
| Amperage            | 15 A    | Is Weather Resistant | No  |
| Indoor/Outdoor      | Indoor  | Mounting Type        | Box |
| Voltage             | 125.0 V |                      |     |

---