



A step up from ordinary, this combination device features a compact switch with a tamper-resistant GFCI outlet. Ideal for use with vents in kitchens and baths, the code-compliant outlet self-tests automatically every three seconds to ensure reliable protection ground fault occurrences, and makes it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Part of the radiant® Collection, it also features sleek, clean lines for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Installs easily in as little as 10 minutes.
- More color options available to fit any style.
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.
- Protects children with a patented shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
- Features durable, high-impact resistant thermoplastic construction.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Number of Receptacles	2
Features	Combination	Outlet Type	GFCI, Indoor, Self-Test, Tamper-Resistant
Warranty Type	1-Year Limited Warranty		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Is Tamper-Resistant	Yes	Number of Gangs	1
Amperage	15 A	Mounting Type	Box
Voltage	125.0 V		