



Pass and Seymour
Turnlok® Portable 2-Foot In-Line 15A Self-Test GFCI with Plug and Connector, Automatic Reset
Part No. 1597TL2A



The perfect option for safely powering portable equipment, outdoors or in, when a GFCI-protected outlet is not accessible. Use this 2-Foot In-Line Portable GFCI (Automatic Reset) when plugging in drills, saws, leaf blowers, pressure washers, power painters, etc. for protection against electrical shock caused by ground-faults.

Designed with Legrand's Turnlok connector to lock plugs in place, preventing accidental disconnection for safer, more reliable operation.

GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

Features & Benefits

Protects against electrical shock caused by ground-fault occurrences.

Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Automatically energizes portable GFCI for use upon plug-in and after loss of primary power.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	China
Outlet Type	GFCI	Application Sector	Residential/Commercial
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	2.0 in	Product Weight US	1.0 lb
Product Depth US	1.75 in	Product Length US	27.75 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	943	cULus Listed	Yes
---------------------	-----	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	No	Amperage	15 A
---------------------	----	----------	------

Is Weather Resistant	No	Indoor/Outdoor	Outdoor
----------------------	----	----------------	---------

NEMA Configuration Code	5-15P, 5-15R	Voltage	125.0 V
-------------------------	--------------	---------	---------
