



radiant Collection
radiant® Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, USB Type A/C, Gray
Part No. 1597IRUSBACGRY



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required (kitchens, bathrooms, laundry rooms, etc). This outlet makes it easy to see and reset electrical trips right where they happen, while also providing two USB connections for keeping phones or tablets charged, no bulky adapter required. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere
 - Provides reliable ground fault protection with a trip indicator light and reset button on the outlet for easy, accessible troubleshooting
- Includes traditional power outlets and two USB Type-A ports for convenient charging. Shares 2.0A charging capacity between both ports
 - Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced
- Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection
 - Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements
- Installs quickly thanks to a redesigned side wire cavity for easier access.
 - Can provide ground fault protection to downstream outlets through feed-thru wiring.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging, USB-C Charging
Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant, USB-Charging	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	E140596
cULus Listed	Yes	CSA File Number	CSA C22.2 No. 223, CSA C22.2 No. 63

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

USB Amperage	2.1 A	Number of USBs	2
Number of Gangs	1	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Wattage	1875 W	Mounting Type	Box
Voltage	125.0 V		