



Pass and Seymour  
**15A, 125V Watertight Connector, Yellow**  
Part No. 15W47



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

## Features & Benefits

Rubber body construction stands up to impacts, oils, chemicals, heat and weather.

Floating blades allow self-alignment with contacts for a firm, even electrical connection.

Terminal screws backed-out, ready-to-wire, saving time and money.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Compression-type cord grip provides watertight seal and 205 lb. pull out strength.

Multiple ring seals between plug and connector ensures protection from water and contaminants.

Quick-drive assembly screws allow for fast installation to save time and money.

NEMA 4, 4X, Watertight. IP65, 66, 67.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Height US	1.85 in	Product Length US	4.03 in
-------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	701645
------------	-----	-----------------	--------

---

Technical Information

---

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Voltage	125.0 V		

---