



Pass and Seymour  
**WaterTight Straight Blade IP67 Connector 15A 250V 6-15R, Yellow**  
Part No. 15W49



Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

|                    |                         |                   |               |
|--------------------|-------------------------|-------------------|---------------|
| Product Line       | Pass & Seymour          | Color             | Yellow        |
| UPC Number         | 785007114409            | Country Of Origin | United States |
| Application Sector | Commercial, Residential | Standard          | UL498         |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 1.85 in | Product Length US | 2.62 in |
|------------------|---------|-------------------|---------|

### Listing Agencies / 3rd Party Agencies

|            |     |                 |    |
|------------|-----|-----------------|----|
| CSA Listed | Yes | CSA File Number | NO |
|------------|-----|-----------------|----|

### Technical Information

|           |             |                 |             |
|-----------|-------------|-----------------|-------------|
| Phase     | Three       | Number of Wires | 3           |
| Amperage  | 15 A        | Number of Poles | Double Pole |
| Wire Size | 18 - 12 AWG |                 |             |