



19.75"W x 24.25"H x 25.00"D

Features & Benefits

Swing-EZ Wall Racks offer flexibility: The 25" deep unit gives the flexibility of mounting equipment where space is a premium and a full size rack cannot be used for small offices.

12-24 threaded EIA hole pattern: Standards compliant to mount numerous types of 19" panels and equipment.

Reinforcement pan attached to bottom of Swing-EZ: Sturdy and holds equipment up to 150lbs.

Self squaring assembly: No additional tools required

Front swing gate with latch pins and bolts on both: Allows you to open swing gate either left or right and easy access to rear of panels and equipment.

Side panels fold flat for shipping: Unfold for easy on site assembly.

Base includes 3" feed through holes: Allows cable delivery from bottom of rack.

- Includes 12-24 mounting screws: Do not have to purchase as separate item

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|---------------|
| Product Line | Ortronics | Color | Black |
| UPC Number | 662875580898 | Country Of Origin | United States |
| Application Sector | Commercial | Type | Rack |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 19.75 in | Product Depth US | 25.0 in |
| Product Height US | 21.0 in | | |

Additional Information

RoHS Conformant

Yes

Product Environmental Profile

Yes
