



Ortronics  
Swing-EZ Wall Rack - Gray - 18.00 in D  
Part No. 19-48-T18DB



19.75"W x 48.00"H x 18.00"D

## Features & Benefits

Swing-EZ Wall Racks offer flexibility.

Front swing gate with latch pins and bolts on both sides: Allows you to open swing gate either left or right and easy access to rear of panels and equipment.

#12-24 threaded EIA hole pattern: Standards compliant to mount numerous types of 19" panels and equipment.

Side panels fold flat for shipping: Unfold for easy on site assembly.

Sturdy and compact: Holds equipment up to 75 lbs.

One-Wrap brand Velcro straps included: Velcro slots located on the rear for cable management.

Includes 12-24 mounting screws : Do not have to purchase as separate item.

## Specifications

### General Info

Product Line	Ortronics	Color	Black
Finish	Powder Coat	UPC Number	662875581109
Country Of Origin	United States	Included	Hardware for mounting
Application Sector	Commercial	Standard	UL1863
Warranty Type	5-Year	Type	Rack

### Dimensions

---

Product Width US	19.75 in	Product Depth US	18.0 in
------------------	----------	------------------	---------

---

Product Height US	49.375 in	Rack Depth	18 in
-------------------	-----------	------------	-------

---

### Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

### Technical Information

---

Rack Units	26 U	Mounting Hole Type	Tapped
------------	------	--------------------	--------

---

Mounting Rail Spacing	19 in	Load Capacity	75 lb
-----------------------	-------	---------------	-------

---

Cable Entry	Back, Front	Frame	Fixed
-------------	-------------	-------	-------

---

Mounting	Wall
----------	------

---