



Wiremold

Discontinued - CabinetMate Plug-In Outlet Center Unit / 120V/20A / 20" long / 8 O/L / 15' cord / Computer Grade Surge
Part No. 2008BDS20R



Eight 20A outlets with t-slots. 15' (406m) cord. Length 20" (55-8mm). Computer grade surge protection, 20 Amps.

Features & Benefits

Eight 20A outlets with t-slots. 6' (1.8m) cord. Length 20" (55-8mm). Computer grade surge protection, 20 Amps.

Specifications

General Info

Product Line	Wiremold	Color	Black, Gray
UPC Number	786776120561	Country Of Origin	Mexico
Material	Aluminum	Product Series	CabinetMate
Number of Receptacles	8	Features	Surge Protection
Application Sector	Commercial, Residential	Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	PIOC

Dimensions

Product Weight US	2.6 lb	Receptacle Spacing	1.25 in
-------------------	--------	--------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single Stage	Cord Length	15 ft
Connection	Cord-ended	Class	75
Amperage	20 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Wiring Method	Cord-ended
NEMA Configuration Code	5-20P, 5-20R	Mounting Type	Spring Clip
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V		
