



The Visual Fault Locator (VFL) Test Adapter for Simplex LC Infinium Mechanical Fiber Connectors allow the visible indicators in the Infinium mechanical fiber connector to be viewed when using a VFL to ensure cable continuity and determine a pass or fail termination.

Features & Benefits

Engineered for optimal performance in professional environments.
Delivers exceptional value by combining quality and affordability.

With a focus on durability, it ensures long-lasting reliability.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875805823	Country Of Origin	United States
Application Sector	Commercial, Data Center	Warranty Type	5-Year
Type	Splice Holder		

Dimensions

Product Width US	1.04 in	Product Depth US	0.27 in
Product Height US	0.51 in		

Technical Information

Operating Temperature Min	-40 °C	Storage Humidity	0-70% RH (Non-Condensing)
Operating Temperature Max	75 °C	Connector Type	LC
Operating Humidity	0-100% RH (Non-Condensing)	Storage Temperature	-40° - 75° C