




Ortronics
Infinium Keyed LC Splice-On Connector (SOC) For 900 Micron Fiber, 50/125 Multimode OM4 Yellow
Part No. 205KKF9GA-50E-C



Legrand pre-polished keyed LC multimode and single-mode connectors provide the same ease of installation and high-quality performance as our line of standard LC pre-polished connectors. Up to thirteen keys/colors of connectors are possible with unique physical keying configurations.

The fusion splicing method is accomplished by fusing the field fiber to the factory-cleaved fiber stub to ensure ease of use and optimal performance. The unique boot allows the entire splice to be concealed and protected.

Features & Benefits

12 color/key configurations available	50/125 microns and 9/125 microns laser-optimized fiber types available
LC Keyed cadapters prevent improper connection of separate networks with common access points	Each LC secure adapter will mate only with same-color LC secure connector
High quality 1.25 mm zirconia ferrules used	Internal keying feature prevents tampering
High quality 1.25 mm zirconia ferrules used	1.6 in boot protects the splice for easy cable management
The solution to managing multiple networks with reduced risks	

Specifications

General Info

Product Line	Ortronics	UPC Number	662875028246
Country Of Origin	United States	Type	Connector

Dimensions

Product Width US	0.236 in	Product Depth US	3.65 in
Product Height US	0.409 in		

Technical Information

Service Life	< 0.2dB typical change, 500 matings	Temperature Rating	20° - 75° C
Insertion Loss	0.15 dB	Fiber Type	OM3/4
Fiber Size	50/125		