




Ortronics  
**Infinium Keyed LC Splice-On Connector (SOC) For 900um Fiber, 50/125 Multimode OM3/4, Rose, 50 Pack**  
Part No. 205KKF9GD-50E-F

Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.



## Features & Benefits

12 color/key configurations available	50/125 microns and 9/125 microns laser-optimized fiber types available
LC Keyed cadapters prevent improper connection of separate networks with common access points	Each LC secure adapter will mate only with same-color LC secure connector
High quality 1.25 mm zirconia ferrules used	Internal keying feature prevents tampering
High quality 1.25 mm zirconia ferrules used	1.6 in boot protects the splice for easy cable management
The solution to managing multiple networks with reduced risks	

## Specifications

### General Info

Product Line	Ortronics	Color	Violet
UPC Number	662875033813	Country Of Origin	United States
Application Sector	Commercial, Data Center	Type	Connector
Boot Color	White		

### Dimensions

Product Width US	0.236 in	Product Depth US	3.65 in
Product Height US	0.409 in		

### Technical Information

Fiber Optic Cable Type	OM4	Service Life	500 matings, < 0.2dB typical change
Splice Type	Fusion	Temperature Rating	-40° - 75° C

Connector Type	Keyed LC	Fiber Size	50/125
----------------	----------	------------	--------