



Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.

Features & Benefits

12 color/key configurations available	50/125 microns and 9/125 microns laser-optimized fiber types available
LC Keyed cadapters prevent improper connection of separate networks with common access points	Each LC secure adapter will mate only with same-color LC secure connector
High quality 1.25 mm zirconia ferrules used	Internal keying feature prevents tampering
High quality 1.25 mm zirconia ferrules used	1.6 in boot protects the splice for easy cable management
The solution to managing multiple networks with reduced risks	

Specifications

General Info

Product Line	Ortronics	UPC Number	662875033936
Country Of Origin	United States	Type	Connector

Dimensions

Product Width US	0.236 in	Product Depth US	3.65 in
Product Height US	0.409 in		

Technical Information

Service Life	500 matings, < 0.2dB typical change	Temperature Rating	-40° - 75° C
Fiber Size	9/125		