



Infinium Splice-On connectors by Legrand® enable fast field terminations while meeting or exceeding industry standards for performance. The entire splice is concealed and protected within the strain relief boot and the UV Cure Protection sleeve cures in seconds, reducing the variables that cause critical errors during installation, so you can finish the job quickly and efficiently.

Legrand 3.0mm Splice-On Connectors have a unique boot that allows the entire splice to be concealed and protected. The addition of an extended brass crimp sleeve provides extra protection to the splice and utilizes the Kevlar for maximized pull strength.

## Features & Benefits

Better Insertion Loss & Return Loss Performance: Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications	Factory-cleaved, pre-polished 900-micron fiber stub: Provides a quicker termination
Available in LC, SC and ST, Single-Mode or Multimode: Multiple connector types available	900-micron boot conceals and protects the splice: Enables better cable management
UV Cure Protection Sleeves: Strain relief boot protects the splice point	3mm Version: 3mm boot protects splice for easy cable management
3mm Version: Brass crimp to protect splice	3mm Version: Tubing insert to accommodate 1.6/2.0/3.0 cordage

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875006008
Country Of Origin	United States		

### Dimensions

Product Width US	0.236 in	Product Depth US	2.46 in
Product Height US	0.4 in		