



Splice-On Connector LC PC OM4

Features & Benefits

- Better Insertion Loss & Return Loss Performance: Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications
- Factory-cleaved, pre-polished 900-micron fiber stub: Provides a quicker termination
- Available in LC, SC and ST, Single-Mode or Multimode: Multiple connector types available
- 900-micron boot conceals and protects the splice: Enables better cable management
- UV Cure Protection Sleeves: Strain relief boot protects the splice point
- 3mm Version: 3mm boot protects splice for easy cable management
- 3mm Version: Brass crimp to protect splice
- 3mm Version: Tubing insert to accommodate 1.6/2.0/3.0 cordage
- Fiber endface types: Endfaces available in PC, APC and UPC

Specifications

General Info

| | | | |
|-------------------|---------------|------------|--------------|
| Product Line | Ortronics | UPC Number | 662875849063 |
| Country Of Origin | United States | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 0.236 in | Product Depth US | 2.46 in |
| Product Height US | 0.4 in | | |