



LC PC reusable connector, field-installable, single-mode, blue housing, white 900 micron boot

Features & Benefits

900um boot protects splice for easy cable management	Includes color coded 900um buffer, boot, cleave protector and extended dust cap for easy fiber identification
No epoxy or polishing and requires no special tools	Reusable termination capability saves time and money while reducing scrap
The VFL window enables immediate feedback on successful termination	

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875257370	Country Of Origin	China
Application Sector	Commercial, Data Center	Type	Connector
Boot Color	White		

Dimensions

Product Width US	1.5 in	Product Height US	0.375 in
------------------	--------	-------------------	----------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Service Life	500 matings, < 0.2dB typical change
Splice Type	Mechanical	Temperature Rating	-40° - 75° C
Connector Type	LC	Fiber Size	9/125