



Hospital-Grade Tamper-Resistant 20A Self-Test Duplex GFCI

## Features & Benefits

Hospital Grade GFCI self-test

One-piece, brass, triple-wipe power contacts for lasting retention.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Type	Outlet

### Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Connection	Back and Side Wire

Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		