



Pass and Seymour  
Discontinued - 20A 125V Hospital-Grade Tamper-Resistant Weather-Resistant Duplex GFCI Receptacle, Black  
Part No. 2097HGTRWRBK



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

## Features & Benefits

Hospital Grade GFCI self-test CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.

## Specifications

### General Info

|                       |                |                         |  |
|-----------------------|----------------|-------------------------|--|
| Product Line          | Pass & Seymour | Replaced by Part Number | PT2097HGTRWRBK   |
| Color                 | Black          | Country Of Origin       | China  |
| Number of Receptacles | 2              | Outlet Type             | Commercial, GFCI, Outdoor, Tamper-Resistant, Weather-Resistant |
| Type                  | Outlet         |                         |  |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.13 in |
| Product Height US | 4.2 in  |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                |         |                 |             |
|----------------|---------|-----------------|-------------|
| Amperage       | 20 A    | Number of Poles | Double Pole |
| Indoor/Outdoor | Outdoor | Voltage         | 125.0 V     |