



Pass and Seymour
Portable 2-Foot In-Line GFCI with Straight Blade Plug and Connector, Automatic Reset
Part No. 2097PC2A



Stay safer on any job, any project with this code-compliant 2-Foot In-Line Portable GFCI (Automatic Reset). Designed for use with portable equipment (drills, saws, power painters, etc.) and providing protection against electrical shock caused by ground faults.

GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

Features & Benefits

| | |
|---|--|
| Protects against electrical shock caused by ground-fault occurrences. | Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced. |
| Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected. | Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged. |
| Automatically energizes portable GFCI for use upon plug-in and after loss of primary power. | |

Specifications

General Info

| | | | |
|--------------------|-------------------------|---------------|-------------------------|
| Product Line | Pass & Seymour | Color | Black |
| Finish | Matte | UPC Number | 785007381689 |
| Country Of Origin | China | Outlet Type | GFCI |
| Application Sector | Commercial, Residential | Warranty Type | 1-Year Limited Warranty |
| Type | Straight Blade | | |

Dimensions

| | | | |
|------------------|---------|-------------------|----------|
| Product Width US | 2.0 in | Product Weight US | 1.0 lb |
| Product Depth US | 1.75 in | Product Length US | 27.75 in |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-----|--------------|-----|
| cULus ListingNumber | 943 | cULus Listed | Yes |
|---------------------|-----|--------------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|----------------|----|---------------------|----|
| Seismic Tested | No | Is Tamper-Resistant | No |
|----------------|----|---------------------|----|

| | | | |
|----------|------|----------------------|----|
| Amperage | 20 A | Is Weather Resistant | No |
|----------|------|----------------------|----|

| | |
|----------------|---------|
| Indoor/Outdoor | Outdoor |
|----------------|---------|
