



Pass and Seymour  
Turnlok® Watertight NEMA 4X/6P Locking Connector, Yellow  
Part No. 25W49



Locking Watertight Connector, 15amp 125volt, NEMA Configuration L6-15, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

|              |                       |                   |               |
|--------------|-----------------------|-------------------|---------------|
| Product Line | Pass & Seymour        | Color             | Yellow        |
| UPC Number   | 785007033083          | Country Of Origin | United States |
| Standard     | UL Listed, CSA Listed |                   |               |

### Technical Information

|          |        |                 |             |
|----------|--------|-----------------|-------------|
| Phase    | Single | Number of Wires | 3           |
| Amperage | 15 A   | Number of Poles | Double Pole |

---

|           |             |                          |                                                                                                                                                                                                                                                                       |
|-----------|-------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire Size | 18 - 12 AWG | Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only)<br>Flammability UL94V0 (boxes & wiring device interiors)<br>Operating Temperature -40°C (without impact) to +60°C<br>continuous UV resistance All exposed material s are UV stabilized |
|-----------|-------------|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

---