



Single-Pole, Back and Side-Wire, Decorator Switch, 15A, 120/277V

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007539035
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Industrial
Standard	UL 20	Type	Switch

Dimensions

Product Width US	1.3 in	Product Depth US	1.03 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
CSA File Number	17446		
Technical Information			
Operating Temperature Min	-4 °F	Contact Rating	15Amp, 120/277Vac
Operating Temperature Max	140 °F	Amperage	15 A
Wire Size	#14 - #10 AWG	Operating Temperature	-20°-60°C, -4°-140°F
Voltage	120/277 V		