



Single-Pole, Back and Side-Wire, Decorator Switch, 15A, 120/277V

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-----------------|
| Product Line | Pass & Seymour | Color | Light Almond |
| Finish | Matte | UPC Number | 785007539042 |
| Country Of Origin | Mexico | Features | Decorator Style |
| Switch Type | Paddle | Application Sector | Industrial |
| Standard | UL 20 | Type | Switch |

Dimensions

| | | | |
|---------------------------------------|---------------|-----------------------|----------------------|
| Product Width US | 1.3 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 17446 | | |
| Technical Information | | | |
| Operating Temperature Min | -4 °F | Contact Rating | 15Amp, 120/277Vac |
| Operating Temperature Max | 140 °F | Amperage | 15 A |
| Wire Size | #14 - #10 AWG | Operating Temperature | -20°-60°C, -4°-140°F |
| Voltage | 120/277 V | | |